Part No.

1110.

Description

Material of Construction:

Î Ï Í Æ073H1000S

Disposable Slot Sampler – 1000mm

High Density Polyethylene (HDPE) - virginConforms to FDA CFR 177.1520

• Conforms to EU Regulations 10/2011

• Conforms to EC Regulations 1935/2004



Method of Construction: Ultrasonic welding

Nominal Length: 968mm

Diameter of Blade: 22mm

Diameter of Outer Tube: 26mm

Nominal Weight of Sampler: 234g



Slot Positions:

Number of Sampling Slots:

Sampling Slot Width: 8mm

Assembly & Packing Environment: Class 100,000 Cleanroom

Individually Bagged? Yes (heat sealed PE bag)

Method of Sterilisation: Gamma Irradiation (25-45kGy)

3

Number of Samplers per Box: 20

BSE/TSE Free: Yes

Recommended Storage Conditions: LAB WHITE TY AND Ambient temperature 1578

WHITE STONE VA 22578 TEL (856) 244-1578 www.qclabequipment.com